



USER MANUAL

WWW.LANEY.CO.UK

DESIGNED & ENGINEERED IN THE UK BY LANEY

L20H - LT-212



HEAD SECURING KIT INSTRUCTIONS

L I O N H E A R T

FITTING INSTRUCTIONS

CONTENTS LIST

- 2 Fixing Plates
- 2 Knurled Thumb Screws
- 4 Plain Washers
- 4 Small Bushed Washers
- 2 Large Bushed Washers
- 4 M5 Pan Head Screws




FITTING INSTRUCTIONS

FITTING INSTRUCTIONS

Your fitting kit includes all the parts to secure the L20H Head Unit to the LT-212 Extension Cabinet.

- 1). Check that you have all the parts to fit a sliding plate on both sides of the Head Unit.
- 2). Using the dimensions in the diagram, locate the position of the threaded insets in the base of the L20H Head - the holes are pre-drilled, but the covering material will need to be pierced in 2 places on each side.



- 3). Screw the fixing plates with the plain and small bushed washers to these inserts in the order in the diagram, so that the plates are held firm, but will slide from side to side.

- 4). Line up the slots in the ends of the plates, with the threaded bushes already fitted into the top of the LT-212 Cabinet, fit the thumb screws and large bushed washers finger tight.

SAVE THESE INSTRUCTIONS



USER MANUAL

MODEL NUMBER:

SERIAL NUMBER:

PLACE OF PURCHASE:

DATE OF PURCHASE:

PLEASE COMPLETE FOR FUTURE REFERENCE

 LANEYAMPLIFICATION

 LANEYAMPLIFICATION

 LANEYAMPS

 LANEYTV

DESIGNED & ENGINEERED IN THE UK BY LANEY

WWW.LANEY.CO.UK

REVISION 1.0